## **Specifications**

For other materials or modifications, please consult TESCOM.

### **OPERATING PARAMETERS**

Pressure rating per criteria of ANSI/ASME B31.3

#### **Maximum Inlet Pressure**

3600 and 6000 psig

248 and 414 bar

#### **Outlet Pressure**

To maximum inlet

### **Design Proof Pressure**

150% maximum rated operating

#### Leakage

**Bubble-tight** 

#### Flow Capacity

 $C_V = 3.3, 6.0, \text{ or } 12.0^*$ 

### MEDIA CONTACT MATERIALS

### Body

303, 316 Stainless Steel

#### Seat

CTFE or Vespel®

#### Diaphragm

Buna-N or Viton®

## O-Rings

Buna-N or Viton®

#### **Back-up Rings**

Teflon®

### **Remaining Parts**

300 Series Stainless Steel


#### **OTHER**

#### Cleaning

CGA 4.1 and ASTM G93

Teflon®, Tefzel®, Vespel®, and Viton® are registered trademarks of E.I. du Pont

\*A secondary pressure drop due to the outlet cross-hole can significantly affect the rated flow capacity. Contact TESCOM for flow curve data when outlet pressure is less than 1000 psig / 69.0 bar.





TESCOM 26-1200 Series dome loaded, high flow pressure reducing regulator is externally loaded with 6000 psig / 414 bar maximum inlet and outlet pressures. The 26-1200 Series offers three orifice sizes and  $C_V$  ratings, balanced main valve, and available external sensing.

# **Applications**

- Rocket engine testing
- Fueling
- · Facilities supply

### **Features and Benefits**

- Diaphragm sensed and highly sensitive
- Modular construction for easy service
- External sensing available for improved accuracy
- Balanced main valve increases seat life
- Mounts in any position
- Low droop and lockup







## **TESCOM**

## 26-1200 Series Regulator Specifications

 $C_{V} = 3.3$ 

**OPERATING PARAMETERS** 

Pressure rating per criteria of ANSI/ASME B31.3

Maximum Inlet Pressure

Stainless Steel Body:

6000 psig / 414 bar

Operating Temperature\*

-40°F to 165°F / -40°C to 74°C

Flow Capacity

 $C_{V} = 3.3$ 

MEDIA CONTACT MATERIALS

Body

303 or 316 Stainless Steel

Seat

CTFE or Vespel®

Diaphragm

Buna-N

**O-Rings** 

Buna-N

**Back-up Rings** 

Teflon®

Gasket

CTFE

**Retaining Ring** 

15-7 Stainless Steel

Valve Cap

17-4 Stainless Steel

**Remaining Parts** 

300 Series Stainless Steel

**OTHER** 

Weight

Stainless Steel: 25 lbs / 11.3 kg

 $C_{V} = 6.0$ 

**OPERATING PARAMETERS** 

Pressure rating per criteria of ANSI/ASME B31.3

**Maximum Inlet Pressure** 

**Vespel:** 6000 psig / 414 bar

CTFE or Tefzel®: 3600 psig / 248 bar

Operating Temperature\*

**Buna-N:** -40°F to 165°F / -40°C to 74°C

**Viton**®: -15°F to 165°F / -26°C to 74°C

**Flow Capacity** 

 $C_{V} = 6.0$ 

MEDIA CONTACT MATERIALS

Body

316 Stainless Steel

Seat

CTFE or Vespel®

Diaphragm

Buna-N or Viton®

**O-Rings** 

Buna-N or Viton®

Back-up Rings

Teflon®

**Connecting Rod** 

17-4 Stainless Steel

Valve

Nitronic 60

**Remaining Parts** 

300 Series Stainless Steel

OTHER

Weight

Stainless Steel: 40 lbs / 18.1 kg

 $C_{V} = 12.0$ 

**OPERATING PARAMETERS** 

Pressure rating per criteria of ANSI/ASME B31.3

**Maximum Inlet Pressure** 

6000 psig / 414 bar

**Operating Temperature\*** 

-15°F to 165°F / -26°C to 74°C

Flow Capacity

 $C_V = 12.0$ 

MEDIA CONTACT MATERIALS

**Body** 

316 Stainless Steel

Seat

Vespel®

Diaphragm

Viton®

O-Rings

Viton®

Back-up Rings

Teflon®

Valve

Nitronic 60

**Remaining Parts** 

300 Series Stainless Steel

**OTHER** 


Weight

Stainless Steel: 60 lbs / 27.2 kg



 $<sup>^{*}</sup>$  For extended temperature applications, consult TESCOM.

# **26-1200 Series Regulator Drawings**






# **TESCOM**

# 26-1200 Series Regulator Flow Chart

For more information on how to read flow curves, please refer to the Flow Curves and Calculations document (debul2007x012) in the TESCOM catalog or on www.tescom.com.

 $C_{V} = 3.3$ 



FLOW RATE - SCFM [SLPM] Nitrogen







# **26-1200 Series Regulator Flow Charts**

For more information on how to read flow curves, please refer to the Flow Curves and Calculations document (debul2007x012) in the TESCOM catalog or on www.tescom.com.





## $C_{V} = 12.0$



The curves above were generated using analytical methods - error is estimated at  $\pm 10\%$ 




## 26-1200 Series Regulator Part Number Selector


Repair Kits, Accessories & Modifications may be available for this product. Please contact TESCOM for more information.

Example for selecting a part number:

 $C_{V} = 3.3$ 

26-12	2	1	-	3	16	1
BASIC SERIES	BODY MATERIAL	LOADING METHOD	INLET AND OUTLET PORT TYPE	DOME PORT	PORT SIZE	ORIFICE SIZE
26-12	<ul><li>2 - 303 Stainless Steel</li><li>6 - 316 Stainless Steel</li></ul>	1 – External	1 – SAE 2 – NPTF 3 – MS33649	1/4" MS33649 1/4" NPTF 1/4" MS33649	<b>12</b> – 3/4" <b>16</b> – 1"	1 – 1/2" 12.7 mm





 $\triangle$ 

WARNING! Do not attempt to select, install, use or maintain this product until you have read and fully understood the TESCOM Safety, Installation and Operation Precautions.

D26120540X012 © 2014 Emerson Process Management Regulator Technologies, Inc. All rights reserved. 09/2014. Tescom, Emerson Process Management, and the Emerson Process Management design are marks of one of the Emerson Process Management group of companies. All other marks are the property of their respective owners.



