Specifications

For questions about this product, please consult TESCOM.

OPERATING PARAMETERS

Pressure rating per criteria of CGA E-4; ASME B31; ASME BPVC

Maximum Inlet Pressure

4500 psig / 310 bar

Maximum Outlet Pressure

15, 50, 125, 250 psig 103, 345, 862, 1724 kPa 1.0, 3.4, 8.6, 17.2 bar

Design Proof Pressure

150% of rated pressure

Leakage

Internal: Bubble-tight

External: Designed to meet < 2 x 10⁻⁸ atm cc/sec He

Operating Temperature

-40°F to 140°F / -40°C to 60°C

Flow Capacity

 $C_{V} = 1.0$

Decaying Inlet Characteristic

For Stainless Steel

0.8 psig / 100 psig 0.06 bar / 6.9 bar

For Neoprene Diaphragm

0.49 psig / 100 psig 0.03 bar / 6.9 bar

MEDIA CONTACT MATERIALS

Bodv

316L Stainless Steel, Nickel-Plated Brass

Seat

PCTFE

Diaphragm

316L Stainless Steel or Neoprene

Filter

10 micron nominal sintered Bronze

10 micron nominal sintered 316 Stainless Steel

Seal

Teflon® or Buna-N

Remaining Parts

Brass, 300 Series Stainless Steel

OTHERS

Connections

Inlet and outlet: 1/2" NPTF Accessories: 1/4" NPTF

Cleaning

CGA 4.1 and ASTM G93

Weight

5.5 lbs / 2.5 kg

Teflon® is a registered trademark of E.I. du Pont de Nemours and Company.



TESCOM SG3 Series is a compact, lightweight, high purity single-stage regulator for specialty, flammable and industrial gas flows of 5-200 SCFM / 141-5600 SLPM. Sensitive, extra long-life metal diaphragm ensures gas purity and integrity. Exceptionally low decaying inlet characteristic provides a stable outlet pressure as inlet pressure varies. User-friendly model number enables the specifier to select optional gauges, relief and shut-off valves and cylinder connections as part of the regulator assembly.

Applications

- Laboratory and Point-of-Use Gas Systems in medical, pharmaceutical, food and beverage and other high purity applications
- High flow, high purity air (CDA and APR) in semiconductor and biotech facilities

Features and Benefits

- Optional neoprene diaphragm provides exceptional sensitivity for precise pressure control
- Cartridge valve design incorporates 10 micron filter to protect the regulator seat and makes service simple








TESCOM

SG3 Series Regulator Drawing








SG3 Series Regulator Flow Charts


For more information on how to read flow curves, please refer to the Flow Curves and Calculations document (debul2007x012) in the TESCOM catalog or on www.tescom.com.

 $C_V = 1.0 \text{ Model}$

Metal Diaphragm



FLOW RATE - SCFM [SLPM] Nitrogen






TESCOM

SG3 Series Regulator Flow Charts


For more information on how to read flow curves, please refer to the Flow Curves and Calculations document (debul2007x012) in the TESCOM catalog or on www.tescom.com.

$C_V = 1.0 \text{ Model}$

Neoprene Diaphragm



FLOW RATE - SCFM [SLPM] Nitrogen







SG3 Series Regulator Part Number Selector

Repair Kits, Accessories & Modifications may be available for this product. Please contact TESCOM for more information.

Base Model

Example for selecting a part number:

| SG3 | 6 | 3 | 1 | | 4 | 0 |
|-----------------|--|---|---|-------------------|--|----------------|
| BASIC SERIES | BODY MATERIAL | OUTLET PRESSURE RANGES | DIAPHRAGM MATERIAL | SEAL MATERIAL | PORTS ² (TOP VIEW) | c _v |
| SG3 | P – Nickel-Plated Brass6 – 316L Stainless Steel | 1 – 15 psig / 103 kPa / 1.0 bar 3 – 50 psig / 345 kPa / 3.5 bar 4 – 125 psig / 862 kPa / 8.6 bar 5 – 250 psig / 1724 kPa / 17.2 bar | 1 – 316L Stainless Steel2 – Neoprene | Teflon® Buna-N | 4 – 4 port OUTLET INLET 5 – 5 port OUTLET INLET | 0 – 1.0 |

Accessories

Ех

| Extension to base mo | del part number: | | | | | | | |
|----------------------|--|------------------------------|-----|----------------------------------|---------------------------|---|--|--|
| SG3XXXXX - | - 0 | 0 | A | A | 1 | 0 | | |
| BASE MODEL NUMBER | | | GAU | GES ² | RELIEF VALVE ¹ | | | |
| | 0 - None P - Plug(s) P - Plug A - psi / kPa D - Teflon® Pipe-away 1 The relief valve is not intended to be a "Pressure Relief Device" as defined by ASME Boiler & Pressure Vessel Code - Section VIII, nor is it intended to be a "Safety Accessory" or "Pressure Limiting Device" as defined by the Pressure Equipment Directive (97/23/EC). The relief valve is intended to indicate a potential substantial country for the production. The principle of the production of | | | | | | | |
| | problem with the regulator and prevent further damage to the regulator. The relief valve is not intended to protect the downstream process equipment. 2GAUGE PRESSURE RANGES | | | | | | | |
| | OUTLET PRESSURE RANGE | | | OUTLET GAUGE PRESSURE RANGE | | | | |
| | SG3X1XXX – 15 psig / 103 kPa / 1.0 bar | | | 0-30 psig / 200 kPa / 2 bar | | | | |
| | SG3X3XXX – 50 psig / 345 kPa / 3.4 bar | | | 0-60 psig / 400 kPa / 4 bar | | | | |
| | SG3X4XXX | – 125 psig / 862 kPa / 8.6 b | ar | 0-160 psig / 1100 kPa / 11 bar | | | | |
| | SG3X5XXX – 250 psig / 1724 kPa / 17.2 bar | | | 0-300 psig / 2000 kPa / 20 bar | | | | |
| | INLE [*] | T PRESSURE RANGE | | INLET GAUGE PRESSURE RANGE | | | | |
| | All | | | 6000 psig / 41,000 kPa / 400 bar | | | | |



SG3 Series Rebuild Kits

Rebuild Kits include replacement cartridges, diaphragms, diaphragm seals, lubrication and instruction sheet.

| KIT PART NUMBER | FOR SG PART NUMBER | | |
|-----------------|--------------------|--|--|
| JT389-8939 | SG3PX1X0 | | |
| JT389-8940 | SG3PX2X0 | | |
| JT389-8941 | SG36X1X0 | | |
| JT389-8942 | SG36X2X0 | | |

 Δ

WARNING! Do not attempt to select, install, use or maintain this product until you have read and fully understood the TESCOM Safety, Installation and Operation Precautions.



