

THE SAME PST CONFIDENCE IN A PORTABLE DEVICE

- > Non-intrusive Ability to Identify Liquid Content of a Sealed Container
- >> Rapid Readings Provide Real-Time Liquid Material Identification
- Detection of Foreign Material Embedded in Containers include: Drugs, Explosives and/or Non-Compliant Materials
- Accurate Resident Database Provides Extensive Liquid Matching
- >> Portable, Lightweight, and Rugged Design for the Elements







perceptivesensors.com

SPECIFICATIONS

PORTABLE-

LIOUID IDENTIFICATION INSIDE CLOSED CONTAINERS. ON THE GO

SCRIPTION 15" X 8.15" X 4.25" (31.1cm X 20.7cm X 10.8cm) 15" bs (2.98 kg) 15" glare Black Matte Finish 16" glare Black Matte Finish 17" glare Black Matte Finish 18" glare Black Matte Finish 19" glare Black Matte Finish 20" glare Black Mat
#5" X 8.15" X 4.25" (31.1cm X 20.7cm X 10.8cm) bs (2.98 kg) glare Black Matte Finish B, Probe, Power 00 MBPS Ethernet Interface (RJ45) 12.4 / 5 GHz Frequency Bands 11 compatible; b/g/n actitive Touch OLED
bs (2.98 kg) Eglare Black Matte Finish B, Probe, Power 00 MBPS Ethernet Interface (RJ45) i: 2.4 / 5 GHz Frequency Bands 11 compatible; b/g/n actitive Touch OLED
bs (2.98 kg) Eglare Black Matte Finish B, Probe, Power 00 MBPS Ethernet Interface (RJ45) i: 2.4 / 5 GHz Frequency Bands 11 compatible; b/g/n actitive Touch OLED
eglare Black Matte Finish B, Probe, Power 00 MBPS Ethernet Interface (RJ45) :: 2.4 / 5 GHz Frequency Bands 11 compatible; b/g/n actitive Touch OLED
eglare Black Matte Finish B, Probe, Power 00 MBPS Ethernet Interface (RJ45) :: 2.4 / 5 GHz Frequency Bands 11 compatible; b/g/n actitive Touch OLED
8, Probe, Power 00 MBPS Ethernet Interface (RJ45) 12 2.4 / 5 GHz Frequency Bands 11 compatible; b/g/n actitive Touch OLED
8, Probe, Power 00 MBPS Ethernet Interface (RJ45) 12 2.4 / 5 GHz Frequency Bands 11 compatible; b/g/n actitive Touch OLED
8, Probe, Power 00 MBPS Ethernet Interface (RJ45) 12 2.4 / 5 GHz Frequency Bands 11 compatible; b/g/n actitive Touch OLED
00 MBPS Ethernet Interface (RJ45) i: 2.4 / 5 GHz Frequency Bands 11 compatible; b/g/n actitive Touch OLED
00 MBPS Ethernet Interface (RJ45) i: 2.4 / 5 GHz Frequency Bands 11 compatible; b/g/n actitive Touch OLED
acitive Touch OLED
days 10
dows 10
ck Replace
out Lithium Ion Battery Pack
d Drive
" X 16" X 7.5" (49cm X 41cm X 19cm)
" x 5.25" x 3" (18.5cm x 13cm x 7cm)
bs (.35kg)
er Resistant Momentary
-contact Infrared.
C to +125°C for sensor temperature
C to +380°C for object temperature a accuracy of 0.5°C over wide temperature
Field of View
Iz Operating Frequency
5" Diameter piezoelectric surface
membrane retainer
C to +40°C Max Operating Temperature
ck release LEMO™
ndard Probe
tom Probe (Inquire)
ernal Hard Drive - USB, 250 GB ery - Spare
OH TO BOTH HERO







perceptivesensors.com

MODEL NUMBER

PORTABLE-

LIQUID IDENTIFICATION INSIDE CLOSED CONTAINERS, ON THE GO.

PST PRODUCT: Portable-ID™ DESCRIPTION BASE MODEL# Base Model includes One Probe, One Battery, One Battery PA600B ('B' is the version) Charger for 110V or 220V ACCESSORIES Standard Probe CU Custom Probe (Inquire) EX External Hard Drive - USB, 250 GB BA Battery - Spare **ORDERING PROCESS** BASE MODEL LIST OF ACCESSORIES PA600A ST (or CU) EX (or left blank)

RESULTING: PA600BST (example)







perceptivesensors.com







info@perceptivesensors.com



Perceptive Sensor Technologies



Zimco Instrumentation Inc.

11141 15 Street NE, Calgary, AB, T3K 0Z5, Canada

Phone: 403-253-8320 Email: info@zimco.ca Website: www.zimco.ca



perceptivesensors.com

Portable-ID™, PA6000B Specifications, Product Images and Information, FluID™, Acoustic Fingerprinting™, and SoundDATA™ are Intellectual Property of Perceptive Sensor Technologies (PST). © Perceptive Sensor Technologies 2020. All Rights Reserved.

